




Rhino Rack 2500 Series - DK455 instruction

CROSSBAR IDENTIFICATION







VA crossbar

EURO crossbar

HD crossbar

			FRONT CROSSBAR						REAR CROSSBAR					
					VA	EURO	HD				VA	EURO	HD	
Vehicle	Date	Crossbar	Front Right Pad/Clamp	Front Left Pad/Clamp	Measurement strip length per side	Measurement strip length per side	Measurement Distance (x)	Foot plate arrow direction	Rear Right Pad/Clamp	Rear Left Pad/Clamp	Measurement strip length per side	Measurement strip length per side	Measurement Distance (x)	Foot plate arrow direction
Hyundai Sonata 4dr sedan 7th Gen LF	15-	1260mm	M415 SUB0148	M414 SUB0148		69mm	1012mm / 39,27/32"	OUT	M414 SUB0374	M415 SUB0374		72mm	1018mm / 40,5/64"	OUT
				Arrow JT	182mm					Arrow UT	185mm			



Rhino Rack 2500 Series - DK455 instruction


Measurement A: CENTRE of door jamb to CENTRE arrow of leg foot plate.


Measurement B: CENTRE of Front leg foot plate arrow to CENTRE of Rear leg foot plate arrow.

Carrying capacity: Roof rack is rated up to 75kg. Please refer to manufacturers handbook for your vehicles maximum roof load capacity. Always use the lower of the two figures.

If your vehicle is not listed on this fitting instruction please refer to your countries Rhino-Rack web site for the latest information.

Direction of Pad Arrow and Foot Plate Arrow





VEHICLE	Date	Measurement A	Measurement B	Load Rating up to (includes racks 5kg/ 11lbs)		
Hyundai Sonata 4dr sedan 7th Gen LF	15-	140mm / 5,33/64"	600mm / 23,5/8"	75kg / 165lbs		

Document No. R980 Issue 1: 17 March 2016 Page 2 of 2